QUICK RESTORATIVE REFERENCE GUIDE

IXED PRODU		DESCRIPTION	ADVANTACES	HEE INDICATORS	CEMENTATION
AAGE	PRODUCT e.max*	With biocompatible lithium disilicate ingots, e.max offers	• Natural translucency	Anterior: Crown, Veneer	CEMENTATION Conventional or Bonded
17. 14		optimized esthetic properties, creating restorations that offer trueto-natural results.	Strength Wear-compatibility Excellent margin adaptation Biocompatibility	Posterior: Crown, Inlay, Onlay	Bonded
à Hall	IPS e.max* ZirCAD Prime	ZirCAD Prime is an extremely versatile material due to its seamless shade progression and Zirconia durability. These restorations are designed by our experienced CAD technicians and milled from a single puck.	High Strength Esthetic Versatile Translucent Biocompatible Exceptional fit Resistant to fracture	Anterior: Crown, Bridge Posterior: Crown, Bridge	Conventional
	IPS e.max* ZirCAD Multi	A premium, highly translucent Zirconia material from Ivoclar Vivadent that provides naturallooking properties, inspired by the esthetics of e.max lithium disilicate.	Metal-free biocompatibility High strength Enhanced translucency Eliminates dark margins Reduces risk of fractures Fixed pricing	Anterior: Crown, Bridge Posterior: Crown, Bridge	Conventional or bonded
	Non/Minimal Prep	Non/Minimal Prep veneers have been made popular by patients for their non-invasive preparation requirements, and their ability to allow the existing tooth shades to shine through.	Minimal Prep (0.2mm- 0.3mm) Highly esthetic Non-invasive Translucent	Anterior: Crown, Veneer	Bonded
	P2Z (Porcelain- to-Zirconia)	P2Z restorations offer the structural strength of Zirconia and the esthetics of e.max. A ceramic overlay provides enhanced light transmission properties and excellent blending capabilities for a natural look.	Proven esthetics Strength Versatility	Anterior: Crown, Bridge Posterior: Crown, Bridge	Conventional
	ZEUS™ Zirconia	Our full-contour ZEUS Zirconia restorations still offer CAD/CAM precision and high strength, but are now more translucent and naturallooking than traditional Zirconia.	Metal free biocompatibility High strength Enhanced translucency Eliminates dark margins Reduces risk of fractures Fixed pricing	Anterior: Crown, Bridge Posterior: Crown, Bridge	Conventional or bonded
	Full Metal	With high noble, semi-precious, and non-precious options, full metal remains a proven material choice due to its longevity and functional success.	Functional success Exceptional fit Strength Durability	Anterior: Crown, Bridge Posterior: Crown, Bridge, Inlay, Onlay	Conventional
	PFM (Porcelain- Fused-to-Metal)	PFM is an exceptional restoration that combines longevity and natural-looking internal characteristics. The underlying coping provides the strength and stability of a natural tooth, while the ceramic coating replicates a natural look.	Longevity Natural-looking internal characteristics Long-span bridges Enhanced esthetics	Anterior: Crown, Bridge Posterior: Crown, Bridge	Conventional
A TE	Composite	Composite restorations offer a true-to-natural restoration designed to parallel the physiological aspects of natural teeth. Technicians can achieve consistent, accurate shade reproduction from case to case.	Excellent margin adaptation High flexural strength Proven durability Proven clinical study	Anterior: Crown, Veneer Posterior: Crown, Bridge, Inlay, Onlay	Dual-cured resin, glass ionomer or luting cements



IMAGE	PRODUCT	DESCRIPTION	ADVANTAGES	USE INDICATORS	CEMENTATION
	Diamond Crown™	Composed of a Poly-Crystalline Nano Ceram material, the biocompatibility of DiamondCrown is extremely high and is non- cytotoxic. The wear ratio of DiamondCrown is the same as natural teeth and gold.	Hydrophobic Fracture-resistant Biocompatible Non-cytotoxic Superior, natural esthetics Longevity & stability	Anterior: Crown, Bridge Posterior: Crown, Bridge, Inlay, Onlay	PolyCrystalline products, DiamondBond™ Adhesive ,and DiamondLink™ Cement

IMPLANT SOLUTIONS				
IMAGE	PRODUCT	DESCRIPTION	ADVANTAGES	
	Implant Restorations	Implant restorations are becoming the standard of care when treating edentulous or partially edentulous	Based on crown type used. See: e.max, ZEUS, P2Z, PFM, and full-metal.	
	patients. Implant-based restorations offer excellent stability, function, and esthetic results. Commonly used abutment materials include Titanium, Zirconia, and gold hue Titanium. Anterior: Crown, Bridge Posterior: Crown, Bridge		, 3	
	Hybrid Denture	Hybrid dentures are proven replacements for removable prostheses worn by edentulous patients. A custom	Functional success Exceptional fit	
TO THE REAL PROPERTY OF THE PARTY OF THE PAR		titanium implant bar is milled using precise CAD/CAM technology. Acrylic teeth are processed to the bar and fixed in the mouth via abutment screws.	•Support •Stability	
	Implant- Supported	These types of dentures are referred to as overdentures and can be removed by the patient. Once the bar	Functional success Exceptional fit	
	Removable Denture	is milled with precise CAD/CAM technology and implanted, the denture is constructed with internal attachments and engaged to the bar for esthetic and functional results.	•Support •Stability	
WOO!	All-on-X	MicroDental's All-on-X is a digitally and prosthetically driven process that achieves optimal workflow efficiencies and accuracy. Every step of the process is designed to give your patient the MicroDental smile, while delivering you the utmost confidence during	Cost Effective & Reduced Chair Time Predictable Fee Structure Chairside & On-site Support at Selected Locations Comprehensive Case Planning & Fully Guided Solutions Streamlined Restorative & Digital Workflows	
	Implant Surgical	As an essential part of successful quided surgery	Personalized Service	
	Guide	treatments, MicroDental Surgical Guides are designed to help you achieve accurate implant placement with confidence. No matter your familiarity with dental implants, our surgical guides and advanced case	Advanced Case Planning Expert Implant Technicians Optimal Accuracy	
D. Ch		planning maximize process efficiencies and eliminate manual errors in implant placement.	Improved Clinical Outcomes Peace of Mind	

IMAGE	PRODUCT	DESCRIPTION	ADVANTAGES	MATERIALS
	Ivotion Milled Digital Dentures	A monolithic solution designed and milled with digital accuracy and superior in all aspects of fit, form, and occlusion. Our specialized removable prosthetics team will case plan and collaborate with your office through a highly efficient workflow. As a final step, our technicians' artistic touch finishes every Ivotion denture to accomplish the life-like aesthetics that your patients will love.	Fewer appointments & chair time Enhanced strength and fit Better retention & fewer sore spots Less post insertion adjustments Digital design & milling accuracy Digital record for quick duplication	
MONTH.	Printed Digital Dentures	Fully-edentulous patients have the option to receive the latest in technology through digitally-designed printed dentures from MicroDental. With the experience of our highly skilled technicians, these complete prosthetic restorations are designed to be true personalized digital dentures.	Less try-in visits No prosthetic variables Improved fit & function Exceeds ISO high impact standards Fracture resistant & high accuracy Digital record for a duplicate set	



MARINE	Complete Dentures	Complete dentures are a viable option for patients that are not candidates for implant-based alternatives. Featuring high-performance materials and a range of denture teeth options, complete dentures offer a functional alternative that is both esthetic and durable.	High biocompatibility Exceptional fit Functional success	Injection acrylic tissue, & teeth
	VisiClear* Flexible Partial Denture	With MicroDental VisiClear Partial Dentures, you can count on a lightweight framework and beautiful esthetics. Made with flexible material and a completely metalfree design, this product allows for improved patient satisfaction, comfort, and easy chairside adjustments.	High biocompatibility Improved comfort Esthetics Repairable & relineable	VisiClear clear resin framework & clasps, with acrylic tissue and teeth
	Valplast* Flexible Partial Denture	With exceptional strength, many partially edentulous patients find the Valplast Flexible Partial to be a comfortable option. This tissue colored flexible framework offers superior esthetics over visible metal clasps. The results of this flexible partial are beautiful, and patient satisfaction is high.	Biocompatibile Improved comfort Esthetics Repairable	Flexible resin tissue & teeth
	Duraflex™ Flexible Partial Denture	Duraflex Partial Dentures are easy to adjust and easy to polish. They are thin, transparent, and resistant to water absorption, making them less likely to absorb stains or odors.	Durable & esthetic Comfortable Repairable & relineable	Flexible acetyl resin & teeth
	Stay Plate	A Stay Plate is a temporary partial denture used while the gums and supporting bone heal after extraction and before getting a partial denture. It will replace the missing tooth or teeth and can assist with chewing and speaking until the partial denture is delivered.	•Functional success •Exceptional fit •Repairable & relineable •Esthetics	Acrylic, teeth, possible wrought wire clasps
	Cast Partial Denture* *Macstudio tier only	Cast Partial Dentures are a premium, strong, cast metal partial. The alloy used allows for a lighter-weight framework that withstands chairside adjustments.	Ease of adjustability Lightweight Functional Prevents natural tooth shifts	Wironium with acrylic tissue and teeth
	Cast Partial Frame* *Classic tier only	Cast Partial Frames are fabricated from alloys that present a strong partial framework that withstands chairside adjustments.	•Functional success •Exceptional fit	Cobalt Chromium, acrylic tissue, teeth

MOUTHGUARD, THERAPY DEVICES, & ORTHOTICS					
IMAGE	PRODUCT	DESCRIPTION	ADVANTAGES	MATERIALS	
	Digital Nightguard	MicroDental's line of digital orthotics includes occlusal devices and nightguards. Dental occlusal devices are necessary for patients with TMD syndrome or severe parafunctional problems. Nightguards provide relief for patients with bruxism while helping to protect their existing dental restorations.	Digital accuracy Ability to reprint from design Strong and flexible Stain and fracture resistant Biocompatible material Enhance patient comfort	KeySplint Soft	
	Hard Nightguard	Designed to protect the dentition, the Hard Nightguard can be worn during the day or at night to provide occlusal comfort. Fabricated for a precise fit and providing maximum rigidity and strength. Not recommended for patients with cosmetic restorations.	Teeth protection Durability Comfort Ease of insertion	Heat-cured hard acrylic & a flat plane	
	All- Thermoplastic Nightguard	The most comfortable acrylic splints, the All- Thermoplastic Nightguard is the easiest to seat and kind to cosmetic restorations. Ideal for cases with missing teeth or unusual draw. This all-thermoflexible acrylic becomes pliable in hot water but remains firm and rigid at mouth temperature.	Teeth protection Durability Comfort Ease of insertion	Heat-cured hard acrylic & a flat plane	
Co-ula	Hard/Soft Nightguard	This nightguard has a soft liner overlay reproduction of the current dental arch form, with an added layer of hard acrylic to provide a flat occlusal plane. It has an even thickness, is contoured to replicate the arch form, and has a flat plane added.	Teeth protection Durability Comfort Ease of insertion	Pressure-formed dual laminate EVA, traditional hard acrylic occlusal, & a flat plane	



	Combo Nightguard	This premium nightguard provides stability and durability over traditional hard acrylic occlusion, combined with easy seating and a comfortable fit. Excellent occlusal durability with fast, comfortable seating, utilizing on-call flexibility in hot water—this is the best of both worlds.	•Teeth protection •Durability •Comfort •Ease of insertion	Hard acrylic occlusion combined with thermo-flexible & a flat plane
	Soft Nightguard	This all-flexible EVA material is used in cases with sensitive or missing teeth or an unusual draw. It is also used for athletic mouthguards. The standard, even thickness is 3mm, and thickness can be added by request. It is soft/flexible in the mouth and contoured.	Teeth protection Durability Comfort Ease of insertion	Pressure-formed EVA
	LVI Removable Orthotic	This orthotic device is recommended by LVI to reprogram the muscles of mastication, and is also used for rehabilitation cases. LVI orthotics are created from a precise LVI bite registration for occlusal accuracy.	Teeth protectionDurabilityComfortEase of insertion	Pressure-formed dual laminate EVA & traditional hard acrylic
Comme	LVI Acetal Resin Orthotics	A new long-term orthotic appliance, recommended by LVI and fabricated by Bill Wade, stabilizes the patient at the physiological bite. Made out of acetal resin, it is flexible enough, so no clasps are required, and is highly durable. It supplies full tooth coverage and color matching.	Durable & strong Rigid but flexible for comfort Natural tooth color Bacteria & stain resistant Biocompatible material	Acetal resin
	ActionGuard™	ActionGuards are fabricated from sturdy yet pliable materials, with the goal of safety for athletes' teeth. This product is available in several different types of styles to suit your patient's needs, ranging from a single-layered ActionGuard to a triple-layered ActionGuard.	Flexible Tough Full dental coverage Customizable occlusal thickness	Pressured-formed soft EVA
The second	TrioClear™ Clear Aligner	TrioClear is an innovative, progressive, three-step clear aligner solution to enhance and improve the process of orthodontic treatment and your patient's smile. They are nearly invisible and straighten teeth by using multiple sets of aligners that gradually move teeth to the ideal position.	Three-step solution Increased gingival coverage TrioDim force divots Minimal attachments Easily duplicated FDA-cleared	100% Recyclable, BPA free

SLEEP SOLUTIONS				
IMAGE	PRODUCT	DESCRIPTION		
	Whole You™ Respire Blue+	Respire Blue+ is a custom, personalized mouthpiece that features a dual block design with interlocking wings. It works by keeping the airway open in any sleep position and allows for a wide range of mouth movement.		
	Whole You™ Respire Pink	Respire Pink features an ergonomic design with telescopic hardware that's fully personalized, ideal for people who experience teeth grinding. It works by allowing lateral and vertical movement, and opens up the airway for better airflow while holding the jaw in a position that prevents it from falling back.		
	The Moses*	This innovative device adds another dimension to oral-appliance therapy. An open anterior design combined with mandibular advancement protrudes the tongue and enlarges the airway.		
Aura	The Moses* Elite	The Moses Elite was introduced as an alternative for bruxer patients. The VisiClear base is strong and flexible offering increased tongue space in a sleek design.		
	EMA*	FDA-approved EMA oral appliance increases airway space by advancing the mandible using interchangeable elastic straps. The EMA elastic straps can be easily changed, allow free lateral excursion, and are latex-free.		

